

## DURAWALL 50



### 50W LED WALL PACK

150 MH Replacement



**480V**

Lumens	6,000	
CCT	3000K, 4000K, 5000K	
CRI	> 75	
Beam Angle	120°	
Operating Voltage	90 - 270 VAC	<b>200 - 480 VAC</b>
Power Consumption	50W	
Driver	Sosen UL Driver	<b>Mean Well</b>
LED Source	Philips 3030 SMD	
Lifespan	> 50,000 Hours	
IP Grade	IP 65	
Body Construction	Die-cast aluminum & toughened glass	
Dimensions	18.5" x 9.4" x 9"	
Weight	14.77 lbs	

### ORDER CODE Example: DW50-BRZ-5K

Fixture	Finish	CCT	Voltage
DW50	BRZ- Bronze	6K- 6000K	___ - 100 - 277 VAC
		5K- 5000K	4V- 200 - 480 VAC
		3K- 3000K	

## DURAWALL 50



### 50W LED WALL PACK

150 MH Replacement



**480V**

Lumens	6,000	
CCT	3000K, 4000K, 5000K	
CRI	> 75	
Beam Angle	120°	
Operating Voltage	90 - 270 VAC	<b>200 - 480 VAC</b>
Power Consumption	50W	
Driver	Sosen UL Driver	<b>Mean Well</b>
LED Source	Philips 3030 SMD	
Lifespan	> 50,000 Hours	
IP Grade	IP 65	
Body Construction	Die-cast aluminum & toughened glass	
Dimensions	18.5" x 9.4" x 9"	
Weight	14.77 lbs	

### ORDER CODE Example: DW50-BRZ-5K

Fixture	Finish	CCT	Voltage
DW50	BRZ- Bronze	6K- 6000K	___ - 100 - 277 VAC
		5K- 5000K	4V- 200 - 480 VAC
		3K- 3000K	