



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E10161643S 1-1/8" Blu Female RCPT *Crouse-Hinds*

Catalog Number	E10161643S
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Cam-Lok J Series E1016 Insulated Receptacle, Up to 400A Continuous, #6 Awg-250 Kcmil, Blue, Female, Thermoplastic Elastomer (Tpe), 1-1/8", Threaded Stud, 600 Vac/DC
Weight per unit	1.0 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	400
connection	1-1/8 In Threaded Stud
dimensions	3.6900 IN X 2.2500 IN X 2.2500 IN
insulation	TPE
Poles	1
Voltage Rating	600 VAC/VDC
Wire Size	6 AWG TO 250 MCM

Dimensions and Weight

Height	2.25
Width	2.25

Descriptions

Description	1-1/8" BLU FEMALE RCPT
extra long description	CRS-H E1016-1643S E1016 F R THRD ST
Features	The Cam-Lok J series from Eaton's Crouse-Hinds Division provides the means to quickly connect and disconnect power systems safely. Cam-Lok is the industry standard for motors, generators, indoor and outdoor lighting distribution panels, and numerous other power applications.
Long Description	Eaton Crouse-Hinds series Cam-Lok J Series E1016 insulated receptacle, Up to 400A continuous, #6 AWG-250 kcmil, Blue, Female, Thermoplastic elastomer (TPE), 1-1/8", Threaded stud, 600 Vac/dc
Product Type	E1016 F R THRD Stud 1 1/8IN BL
Special Features	NEMA 3R Enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662275128737
Manufacturers Part Number	E1016-1643S
UPC	662275128737

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Insulated receptacle

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	-40 To 105 Deg C
Mounting	Threaded Panel
standard	UL 498, CSA C22.89