



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E10162317 WHT M-FM-FM T Conn *Crouse-Hinds*

Catalog Number	E10162317
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Cam-Lok J Series E1016 Three Way "T" Connector, Up to 400A Continuous, White, Male/Female/Female, Thermoplastic Elastomer (Tpe), Tapping, Lay Down, 600 Vac/DC
Weight per unit	1.0 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	400
connection	Connectors
dimensions	5.0000 IN X 1.5000 IN X 3.3100 IN
Poles	1
Voltage Rating	600 VAC/VDC
Wire Size	2 To 4/0 AWG

Dimensions and Weight

Size	1.50 in Diamater X 3.88 in Length
------	-----------------------------------

Descriptions

Description	WHT M-FM-FM T CONN
extra long description	CRS-H E1016-2317 E1016 MFF TAP TEE
Features	The Cam-Lok J series from Eaton's Crouse-Hinds Division provides the means to quickly connect and disconnect power systems safely. Cam-Lok is the industry standard for motors, generators, indoor and outdoor lighting distribution panels, and numerous other power applications.
Long Description	Eaton Crouse-Hinds series Cam-Lok J Series E1016 three way "T" connector, Up to 400A continuous, White, Male/female/female, Thermoplastic elastomer (TPE), Tapping, Lay down, 600 Vac/dc
Product Type	E1016 MFF Tap Tee WH
Special Features	NEMA 3R Enclosure

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00662275129826
Manufacturers Part Number	E1016-2317
UPC	662275129826

Taxonomies, Classifications, and Categories

Category Description	Pin & Sleeve Devices
Type	Three way "T" connector



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	1

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
environmental conditions	-40 To 105 Deg C
standard	UL, CSA