

# Eaton E22KB53A

Catalog Number: E22KB53A

Eaton E22 pushbutton, E22 Pushbutton, 22.5 mm, Non-metallic Heavy-Duty, Cam 2, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Two-position, Key, 1NO, Right and left, Black bezel, 45° Throw

## General specifications



**Product Name**  
Eaton E22 pushbutton

**Catalog Number**  
E22KB53A

**UPC**  
782113831589

**Product Length/Depth**  
2.5 in

**Product Height**  
2 in

**Product Width**  
4.5 in

**Product Weight**  
0.2 lb

**Warranty**  
Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

**Compliances**  
CE Marked

**Certifications**  
CSA Certified  
IEC 947-5-1 MTTA  
UL 508  
Lloyd's Register Certified

## Catalog Notes

Key removal from maintained position only, will accept a maximum of 2 contact blocks (4 circuits) with supplied 3-way mounting adapter. Optional 5-way adapter will accept a maximum of 5 contact blocks (10 circuits)

## defaultTaxonomyAttributeLabel

### Type

22.5 mm, Non-metallic Heavy-Duty

### Bezel

Black

### Cam code

Cam 2

### Key removal position

Right and left

### Enclosure

NEMA 3R

NEMA 4X

NEMA 4

NEMA 13

NEMA 3

NEMA 12

### Actuator

Key

### Contact configuration

1 NO

### Illumination

Non-illuminated

### Series

E22

### Number of positions

2

### Throw type

45 °

## Resources

### Brochures

[Pushbuttons, Indicating lights, Selector switches and Stacklights](#)

### Specifications and datasheets

[Eaton Specification Sheet - E22KB53A](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)