



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E44MR16RICAT 4" Ic Low Volt Shallow Led HSNB Remodel GX5.3 Base *Cooper Lighting Solutions*

Catalog Number	E44MR16RICAT
Manufacturer	Cooper Lighting Solutions
Description	4" Ultra-Shallow Recessed Low Voltage Remodeler Housing, MR16 10W Max
Weight per unit	0.8200 (lbs/each)
Product Category	Lighting

Features

amperage rating	.0833 at 120V
Ballast Type	N/A
Lamp Type	LED/Halogen
Number of Lamps	1
Socket Type	Gx5.3 / bi-pin 12V LED MR16
Voltage Rating	120V
Wattage	10 W

Descriptions

Description	4" IC LOW VOLT SHALLOW LED HSNB REMODEL GX5.3 BASE
extra long description	CLS E44MR16RICAT 4" ULTRA SHAL RMDL
Long Description	4" Ultra-Shallow Recessed Low Voltage Remodeler Housing, MR16 10W Max
Product Type	4" Ultra Shal RMDL, Icat, 10W MR16, Unv
Special Features	Optimized for use with LED MR16 lamps

Manufacturer Information

Brand	HALO
GTIN	00080083818341
Manufacturers Part Number	E44MR16RICAT
UPC	080083818341

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	4" E44 Housings

Packaging

Carton	1
Weight Per each	0.82

Uses, Certifications, and Standards

Application	lighting
standard	N/A