

Eaton E49G31UP3

Catalog Number: E49G31UP3

Mini Complete Limit Switch, E49, Adjustable side rotary lever, Screw Terminals, 5A at 250 Vac, 5A at 30 Vdc, 5 mm-50 cm/s, 1NO-1NC



General specifications

Product Name	Catalog Number
Eaton E49 mini metal limit switch	E49G31UP3
UPC	Product Length/Depth
786685102108	2.62 in
Product Height	Product Width
1.89 in	1.1 in
Product Weight	Warranty
0.42 lb	1 year
Compliances	
RoHS Compliant	

defaultTaxonomyAttributeLabel

Contact Rating

5A at 250 Vac, 5A at 30 Vdc

Enclosure material

Cast zinc

Actuator

Adjustable side rotary lever

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Series

E49

Operating temperature - max

149 °F

Operating temperature - min

23 °F

Environmental rating

IP65

Maximum AC current

5 A continuous

Maximum DC current

5 A at 30 Vdc

Operating speed

5 mm-50 cm/s

Resources

Brochures

[E49 Mini Metal Limit switches](#)

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E49G31UP3](#)