

Eaton E50ANR1

Catalog Number: E50ANR1

Eaton E50 NEMA heavy duty plug-in limit switch, Assembly, Screw Terminals, 10A at 12 Vac, 1A at 125 Vdc, Side rotary, 1NO-1NC, Die cast zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, Neon, 120 Vac, 10A continuous, 1A, 10° to 200°F, E50



General specifications

Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit E50ANR1 switch	UPC 782113308845
Product Length/Depth	Product Height
4.22 in	2.46 in
Product Width	Product Weight
1.54 in	0.41 lb
Warranty	Compliances
1 year	RoHS Compliant
Certifications	
CSA Certified UL Listed	

defaultTaxonomyAttributeLabel

Type

Assembly

Contact Rating

10A at 12 Vac, 1A at 125 Vdc

Enclosure material

Die cast zinc

Actuator

Side rotary

Connection

Screw terminal

Contact configuration

1 NO-1 NC

Series

E50

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Light unit voltage

120 Vac

Maximum AC current

10 A continuous

Maximum DC current

1 A

LED indicator

Neon

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50ANR1](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)