

# Eaton E50DT1

Catalog Number: E50DT1

Eaton E50 NEMA heavy duty plug-in limit switch, Top pushbutton, Die cast zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, 14° to 201°F (-10° to 94°C), E50

## General specifications



Product Name	Catalog Number
Eaton E50 NEMA heavy duty plug-in limit switch	E50DT1
	UPC
	782113290591

Product Length/Depth	Product Height
1.48 in	1.78 in

Product Width	Product Weight
1.54 in	0.11 lb

Warranty	Compliances
1 year	RoHS Compliant

**Certifications**  
CSA Certified  
UL Recognized

## defaultTaxonomyAttributeLabel

### Enclosure material

Die cast zinc

### Actuator

Top pushbutton

### Series

E50

### Operating temperature - max

201 °F

### Operating temperature - min

14 °F

### Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,  
NEMA 6P, NEMA 13, IP67

## Resources

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - E50DT1](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)