

Eaton E50KL203

Catalog Number: E50KL203

E50 Series Limit Switch Operator, Lever for Side Rotary Switches,
Roller: Nylatron enclosure, Lever: Die Cast Zinc

General specifications



Product Name **Catalog Number**

Eaton E50 NEMA heavy duty plug-in limit E50KL203
switch operator

UPC

782113298511

Product Length/Depth

1.9 in

Product Height

2.87 in

Product Width

0.93 in

Product Weight

0.06 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Listed

CSA Certified

CE

Catalog Notes

Lever length is from the operating shaft
axis to the roller axis

defaultTaxonomyAttributeLabel

Enclosure material

Lever: die Cast Zinc

Roller: nylatron

Switch type

Lever for side rotary switches

Operating temperature - max

201 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,

NEMA 6P, NEMA 13, IP67, IP69K

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL203](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)