

Eaton E50KL226

Catalog Number: E50KL226

Limit Switch Operator, E50 Heavy Duty Plug In, Accessory, Adjustable rod, Used with side rotary, Bendable steel

General specifications



Product Name Catalog Number

Eaton E50 NEMA heavy duty plug-in limit switch operator E50KL226

UPC

782113290966

Product Length/Depth

12 in

Product Height

0.38 in

Product Width

1.12 in

Product Weight

0.3 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Listed

CSA Certified

CE



Powering Business Worldwide

Type

Accessory

Used with

Used with side rotary

Actuator

Adjustable rod

Series

E50 heavy duty plug in

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Material

Bendable steel

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL226](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)