

Eaton E50KL546

Catalog Number: E50KL546

Limit Switch Lever, E50, Accessory, Standard roller, 0.71 in-oz min. return, Used with side rotary, Nylatron

General specifications



Product Name Catalog Number

Eaton E50 NEMA heavy duty plug-in limit E50KL546
switch operator

UPC

782113298689

Product Length/Depth

2.72 in

Product Height

0.61 in

Product Width

0.75 in

Product Weight

0.15 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Listed

CSA Certified

CE

defaultTaxonomyAttributeLabel

Type

Accessory

Used with

Used with side rotary

Actuator

Standard roller

Torque rating

0.71 in-oz min return

Series

E50

Operating temperature - max

200 °F

Operating temperature - min

10 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Material

Nylatron

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50KL546](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)