

Eaton E50RB

Catalog Number: E50RB

Eaton E50 NEMA heavy duty plug-in limit switch, Screw Terminals, Surface, Die cast zinc, NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, -40° to 250°F (-40° to 121°C), E50 Heavy Duty Plug In, Neutral position 5° travel

General specifications



| | |
|--|---------------------|
| Product Name | Catalog Number |
| Eaton E50 NEMA heavy duty plug-in limit E50RB switch | UPC 782113290737 |
| Product Length/Depth | Product Height |
| 2.92 in | 1.06 in |
| Product Width | Product Weight |
| 1.54 in | 0.11 lb |
| Warranty | Compliances |
| 1 year | RoHS Compliant |
| Certifications | |
| UL Recognized CSA Certified | |

defaultTaxonomyAttributeLabel

Enclosure material

Die cast zinc

Connection

Screw terminal

Series

E50 heavy duty plug in

Switch type

Neutral position 5 ° travel

Operating temperature - max

250 °F

Operating temperature - min

-40 °F

Environmental rating

NEMA 1, NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 6,
NEMA 6P, NEMA 13, IP67

Mounting method

Surface

Resources

Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - E50RB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)