

Eaton E53KAL30A2SA

Catalog Number: E53KAL30A2SA

Eaton E53 tubular capacitive proximity sensor, Threaded, Straight, 30 mm, Shielded, Output ON, Dual key micro, 300 mA Solid State Output, 3 pin, 2-wire AC, NO, 20-250V

General specifications



Product Name	Catalog Number
Eaton E53 tubular capacitive proximity sensor	E53KAL30A2SA
	UPC
	782114012901
Product Length/Depth	Product Height
3.94 in	1.18 in
Product Width	Product Weight
1.18 in	0.25 lb
Warranty	
1 year	

Type

Threaded

Contact Rating

300 mA Solid State Output

Actuator function

Shielded

Enclosure material

Mounting nuts

POM

Nylon PA66

Connection

Dual key micro

Contact configuration

2-wire AC, NO

Series

E53

Input voltage

20-250 V

LED indicator

Output ON

Output

Maximum AC current

300 mA

Number of pins

3

Operating temperature - max

158 °F

Operating temperature - min

-13 °F

Environmental rating

NEMA 1, NEMA 2, NEMA 3, NEMA 3S, NEMA 4, NEMA 12,

NEMA 13, IP65

Brochures

Sensing solutions—versatile, robust and innovative

Catalogs

Product Range Catalog Sensors – products, basic information, applications

Eaton's Volume 8—Sensing Solutions

Specifications and datasheets

Eaton Specification Sheet - E53KAL30A2SA



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)