



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



E57LAL18A2E 18MM STD Ind Prox 2W Ac Eaton Corp

Catalog Number	E57LAL18A2E
Manufacturer	Eaton Corp
Description	Premium+ Inductive Proximity Sensor, E57, Straight, 18 MM, Unshielded, 360° Viewable Led, 6.6 FT, 250 Ma At 250V, <3% Sensing Range, PVC, 2-Wire Ac, No, 20-250V
Weight per unit	0.7000 (lbs/each)
Product Category	Inductive Proximity Sensor

Features

Accuracy	< 3% sensing range
dimensions	2.6000 IN X 0.7100 IN X 0.7100 IN
media	Yes
thread size/sense distance	18mm/8mm
Voltage Rating	18

Dimensions and Weight

Depth	18
-------	----

Descriptions

Description	18MM STD IND PROX 2W AC
extra long description	ETN E57LAL18A2E 18MM STD IND PROX 2
Features	E57G general purpose sensors are a cost-effective solution that is optimised to include only those functions that are necessary for basic, reliable sensing without lacking the performance or features you expect in an Eaton product. These sensors include various diameter options designed to fit a variety of applications.
Long Description	Premium+ Inductive Proximity Sensor, E57, Straight, 18 mm, Unshielded, 360° viewable LED, 6.6 ft, 250 mA at 250V, <3% sensing range, PVC, 2-wire AC, NO, 20-250V
Product Type	18MM STD Ind Prox 2W Ac

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113743011
Manufacturers Part Number	E57LAL18A2E
UPC	782113743011

Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Inductive Proximity Sensor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 0.7

Uses, Certifications, and Standards

Application Stationary Mach Equip In Factory - Other Stationary Machinery
and Equipment - In Factory

environmental conditions NEMA 4, NEMA 4X, NEMA 6, NEMA 6P, NEMA 12, NEMA 13,
IP67, IP69K

standard UL Listed, CSA Certified, CE Marked