

# Eaton E64CAT2T

Catalog Number: E64CAT2T

Eaton Photoelectric Sensor, E64, Diffuse Reflective, Right Angle, Output (yellow), stability (green), power ON (green), Screw Terminals, 3A at 250 Vac/30 Vdc, SPST relay Form C, 20-240 Vac, 20-60 Vdc

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton E64 series photoelectric sensor terminal base	E64CAT2T
	<b>UPC</b>
	782113435497
<b>Product Length/Depth</b>	<b>Product Height</b>
3.97 in	0.81 in
<b>Product Width</b>	<b>Product Weight</b>
2.74 in	0.41 lb
<b>Warranty</b>	
3 year	

## defaultTaxonomyAttributeLabel

### Contact Rating

3A at 250 Vac/30 Vdc

### Enclosure material

PBT 30% glass fiber-reinforced

### Connection

Screw terminal

### Contact configuration

SPST relay form C

### Series

E64

### Sensor type

Diffuse reflective

### Input voltage

20-240 Vac, 20-60 Vdc

### LED indicator

Output: yellow

Stability: green

Power: green

### Maximum AC current

3 A

### Maximum DC current

3 A

### Operating temperature - max

55 °C

### Operating temperature - min

-25 °C

### Environmental rating

IP67

## Resources

### Catalogs

[Eaton's Volume 8—Sensing Solutions](#)

### Specifications and datasheets

[Eaton Specification Sheet - E64CAT2T](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)