



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EABY26 3/4" Cond Body & CVR

*Crouse-Hinds*

Catalog Number	EABY26
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Eab Conduit Outlet Box With Cover, 3" Cover Opening Diameter, Feraloy Iron Alloy, Y Shape, 3/4"
Weight per unit	4.4 (lbs/each)
Product Category	Bodies & Covers

### Features

Cable Entry	(4) Side, (1) Down
dimensions	5.5600 IN X 2.7800 IN X 4.6600 IN
Material	FERALOY IRON ALLOY

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Description	3/4" COND BODY & CVR
extra long description	CRS-H EABY26 3/4 Y IRON GRP A B ROU
Features	Crouse-Hinds series EAB and EAJ explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes.EAB and EAJ outlet boxes are manufactured in five different hub configurations with mounting feet and 16 pitch cover threads.
Long Description	Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, Y shape, 3/4"
Product Type	3/4 Y Iron GRP A B Round Base Outlet CVR
Special Features	With Cover

### Manufacturer Information

Brand	Eaton
GTIN	00782274249001
Manufacturers Part Number	EABY26
UPC	782274249001

### Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	4.4

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 886, CSA C22.2