



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EAJL26 3/4 NPT L Iron Round Base 3 3/16 CVR *Crouse-Hinds*

Catalog Number	EAJL26
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Eaj Conduit Outlet Box With Cover, 3-3/16" Cover Opening Diameter, Feraloy Iron Alloy, L Shape, 3/4"
Weight per unit	4.1 (lbs/each)
Product Category	Bodies & Covers

Features

Cable Entry	(2) Side
dimensions	4.6600 IN X 2.7800 IN X 4.6600 IN
Material	FERALOY IRON ALLOY

Dimensions and Weight

Size	3/4 in
------	--------

Descriptions

Description	3/4 NPT L IRON ROUND BASE 3 3/16 CVR
extra long description	CRS-H EAJL26 3/4 NPT L IRON ROUND B
Features	Crouse-Hinds series EAB and EAJ explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes.EAB and EAJ outlet boxes are manufactured in five different hub configurations with mounting feet and 16 pitch cover threads.
Long Description	Eaton Crouse-Hinds series Condulet EAJ conduit outlet box with cover, 3-3/16" cover opening diameter, Feraloy iron alloy, L shape, 3/4"
Product Type	3/4 NPT L Iron Round Base 3 3/16 CVR
Special Features	With Cover, Cover Opening Diameter 3-3/16 In

Manufacturer Information

Brand	Crouse-Hinds
GTIN	00782274943848
Manufacturers Part Number	EAJL26
UPC	782274943848

Taxonomies, Classifications, and Categories

Type	Conduit outlet box with cover
------	-------------------------------

Packaging

Carton	1
Weight Per each	4.1



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 886, CSA C22.2