

Complete Cables

Accessory	Description	For Use With...	Catalog Number	Price	Discount Code
Programming Cables					
	SUB-D 9-pole, serial, 2m (6.5 ft)	EASY500 EASY700	EASY-PC-CAB	201	E20
		EASY800 MFD-CP8	EASY800-PC-CAB	215	E20
	USB, 2m (6.5 ft)	EASY500 EASY700	EASY-USB-CAB	325	E20
		EASY800 MFD-CP8	EASY800-USB-CAB	325	E20
Point-to-point Connection Cable					
	Serial interface for connecting EASY800 to MFD-...CP8 Can be configured as required with separate plug Length: 5 m (16.4 ft), can be cut as needed	EASY800 MFD-CP8	MFD-800-CAB5	270	E20
Network Cables					
	Cable length: 0.3 m (0.98 ft)	easy-NET	EASY-NT-30	26	E20
	Cable length: 0.8 m (2.62 ft)		EASY-NT-80	44	E20
	Cable length: 1.5 m (4.92 ft)		EASY-NT-150	68	E20
PROFIBUS-DP Bus Connector Plug					
	9-pin connector Cable entry Angled 90°	PROFIBUS-DP	ZB4-209-DS2	225	E23
	Metallic insulated housing Maximum transfer rate: 12 Mbit/s Integrated switch for bus terminating resistors Terminal block for two cable entries with straight or angled 90°, as needed	EASY204-DP	ZB4-209-DS3	225	E22

Turn to next page for more cabling options

Display Adapter

Accessory	Description	For Use With...	Catalog Number	Price	Discount Code
Display Adapter					
	Connection of EASY800 to MI4 operator panel, in conjunction with EASY800-PC-CAB	EASY800 / MFD-CP8 EASY800-PC-CAB	ZB4-03B-AD1	150	E22