

Eaton EBMBA

Catalog Number: EBMBA

Eaton Crouse-Hinds series EBMB circuit breaker enclosure, 10A through 70A, Without circuit breaker, Bolted/ground joint/gasketed cover construction, Copper-free aluminum



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EBMB circuit breaker enclosure	EBMBA
	UPC
	782274441733
Product Length/Depth	Product Height
14.78 in	18.25 in
Product Width	Product Weight
10.25 in	84.1 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

3R

4

7

9

12

Product specifications

Enclosure

Without circuit breaker

Amperage Rating

10 A through 70 A

Enclosure cover construction

Bolted/ground joint/gasketed

Enclosure material

Copper-free aluminum

Resources

3D models

[SP3D Design Package - EBMB Explosionproof Circuit Breakers](#)

Catalogs

[EBMB Series Explosionproof Circuit Breakers catalog page](#)

Certification reports

[EBMB Explosionproof Circuit Breakers UL certification](#)

[EBMB Explosionproof Circuit Breakers Canadian certification](#)

Installation instructions

[IF 1616 - Flange Gasket Replacement Kit](#)

[IF 1149 - Wiring](#)

[IF 1150 - EBM Motor Control Series Combination Line Starters, Motor Starters, Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - EBMB](#)