



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ECLK312 1 X 12 Div 1 Flex CPLG Male-Female *Crouse-Hinds*

Catalog Number	ECLK312
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Eclk Coupling, 12" Flexible Length, Male Connection One End, Female Connection One End, Forged Brass, 1" Trade Size
Weight per unit	4.1 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

### Features

connection	Female Union X Male Threaded
dimensions	17.0000 IN X 2.1300 IN X 2.1300 IN
outside diameter	2-1/8

### Dimensions and Weight

Length	12
--------	----

### Descriptions

Description	1 X 12 DIV 1 FLEX CPLG MALE-FEMALE
extra long description	CRS-H ECLK312 1 X 12 DIV 1 FLEX CPL
Features	Crouse-Hinds series EC explosionproof couplings are used in hazardous areas where a flexible member is required in a conduit system to accomplish difficult bends, or to allow for movement or vibration of connected equipment or units.
Long Description	Eaton Crouse-Hinds series ECLK coupling, 12" flexible length, Male connection one end, female connection one end, Forged brass, 1" trade size
Product Type	1 X 12 Div 1 Flex CPLG Male-Female
Special Features	Liquidtight

### Manufacturer Information

Brand	Eaton
GTIN	00782274261607
Manufacturers Part Number	ECLK312
UPC	782274261607

### Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	COUPLING

### Trade Size

Trade Size	1 in
------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	4.05

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure standard	Class I Div 1 Group A B C D, Class II Div I Group E F G, Class III UL 1203