



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EDB3225 Edb 22KA @ 240 V 3 Pole 225AS Load Term *Eaton Corp*

Catalog Number	EDB3225
Manufacturer	Eaton Corp
Description	Series C, F-Frame Molded Case Circuit Breaker, 225A, Three-Pole, Fixed Thermal Magnetic Trip Edb Breaker
Weight per unit	4.3 (lbs/each)
Product Category	3 Pole

Features

Current Rating	225 A
dimensions	3.3800 IN X 4.1300 IN X 6.0000 IN
media	Yes
Poles	Three-pole
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	240 Vac, 125 Vdc

Descriptions

Description	EDB 22KA @ 240 V 3 POLE 225AS LOAD TERM
extra long description	ETN EDB3225 EDB 22kA @240 V, 3P 225
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Series C, F-frame molded case circuit breaker, 225A, Three-pole, Fixed thermal magnetic trip EDB breaker
Product Type	Edb 22KA @240 V, 3P 225 As, Load Term

Manufacturer Information

Brand	Eaton
GTIN	00782116152728
Manufacturers Part Number	EDB3225
UPC	782116152728

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	4.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMs
Frequency Rating	50 to 60 Hz
standard	UL Listed