

Eaton EDS21275

Catalog Number: EDS21275

Eaton Crouse-Hinds series EDS selector switch control station, With selector switch, With one 3/4" hub, Feraloy iron alloy, Three-position, four-circuit, 4, 1, Single-gang, 3, Dead end, 3/4", 600 Vac



General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EDS selector switch control station	EDS21275
	UPC
	782274764702
Product Length/Depth	Product Height
3.5 in	5.91 in
Product Width	Product Weight
5.44 in	8.11 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

7

9

Product specifications

Enclosure type

With selector switch

Voltage rating

600 Vac

Number of gangs

Single-gang

Number of devices

1

Normal position

Three-position, four-circuit

Style

Dead end

Trade size

3/4"

Number Of Positions

3

Number of circuits

4

Hub style

With one 3/4" hub

Material

Feraloy iron alloy

Resources

3D models

[SP3D Design Package - EDS and EFS Explosionproof Control Stations](#)

Catalogs

[EDS/EDSX Hazardous Area Control Stations catalog page](#)

Certification reports

[EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations UL certification](#)

[EDS and EFS Explosionproof Pushbutton, Pilot Light, and Selector Switch Control Stations Canadian certification](#)

Installation instructions

[IF 328 - EDS, EFS, EDSC and EFSC Single- and Two-gang Device Bodies](#)

IF 372 - EDS Notice

IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations

Specifications and datasheets

Eaton Specification Sheet - EDS21275



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)