

# Eaton EGB3015FFG

Catalog Number: EGB3015FFG

Eaton Series G molded case circuit breaker, EG-frame, EG, Complete breaker, Fixed thermal, fixed magnetic trip type, Three-pole, 15A, 600Y/347 Vac, 25 kAIC at 240 Vac, 18 kAIC at 480 Vac, Line and load, 50/60 Hz



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Series G complete molded case circuit breaker	EGB3015FFG
	<b>UPC</b>
	782116131280
<b>Product Length/Depth</b>	<b>Product Height</b>
2.99 in	5.5 in
<b>Product Width</b>	<b>Product Weight</b>
3 in	3 lb
<b>Warranty</b>	<b>Compliances</b>
Eaton Selling Policy 25-000, one (1) year CE Marked from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Certifications</b>
	IEC Rated
	UL Listed
	CSA Certified

## defaultTaxonomyAttributeLabel

### Type

Complete breaker

### Amperage Rating

15 A

### Voltage rating

600Y/347 Vac

### Trip Type

Fixed thermal, fixed magnetic

### Circuit breaker type

EG

### Circuit breaker frame type

Complete breaker

### Series

Series G

### Terminals

Line and load

### Frame

EG

### Frequency rating

50/60 Hz

### Interrupt rating

18 kAIC at 480 Vac

25 kAIC at 240 Vac

### Number of poles

Three-pole

## Resources

### Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

### Brochures

[Multi-wire lugs product aid](#)

[Comprehensive circuit protection for control panel applications](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Motor protection circuit breakers product aid](#)

[Series G MCCB quick selector](#)

[MOEM MCCB Product Selection Guide](#)

[StrandAble terminals product aid](#)

[High performance operating handles for Series G circuit breakers product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Current limiting molded case circuit breaker module product aid](#)

[Circuit breaker motor operators product aid](#)

[Current limiting molded case circuit breaker module for series G, JG and CL](#)

[Series G Molded Case Circuit Breakers - Quick Selector](#)

[Molded case circuit breakers providing higher levels of selective coordination product aid](#)

[Breaker service centers](#)

### Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

### Drawings

[EG-frame Molded Case Circuit Breaker Drawing](#)

### Specifications and datasheets

[NG and ND-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - EGB3015FFG](#)

[MOEM MCCB product selection guide](#)

[EG-Frame Circuit Breaker 15-160 Amperes Technical Data](#)

### Time/current curves

[Eaton Series G type EGB, EGE, EGS, EGH, EGC, and EGK circuit breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)