

Specifications



Photo is representative



Eaton EHD3030

Eaton Series C complete molded case circuit breaker, F-frame, EHD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 30 A, Load side, 50/60 Hz

Product specifications

AMPERAGE RATING	30 A
TRIP TYPE	T186
CIRCUIT BREAKER TYPE	EHD
CIRCUIT BREAKER FRAME TYPE	Complete breaker
SERIES	Series C

General specifications

PRODUCT NAME	Eaton Series C complete molded case circuit breaker	TERMINALS	Load side
CATALOG NUMBER	EHD3030	FRAME	F
UPC	786679317099	FREQUENCY RATING	50/60 Hz
PRODUCT LENGTH/DEPTH	3.38 in	INTERRUPT RATING	14 kAIC at 480 Vac 18 kAIC at 240 Vac
PRODUCT HEIGHT	6 in	NUMBER OF POLES	Three-pole
PRODUCT WIDTH	4.13 in		
PRODUCT WEIGHT	4.5 lb		
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.		
CERTIFICATIONS	UL Listed		

Specifications



Photo is representative



Eaton EHD3030

Eaton Series C complete molded case circuit breaker, F-frame, EHD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 30 A, Load side, 50/60 Hz

Product specifications

AMPERAGE RATING	30 A
TRIP TYPE	T186
CIRCUIT BREAKER TYPE	EHD
CIRCUIT BREAKER FRAME TYPE	Complete breaker
SERIES	Series C

General specifications

PRODUCT NAME	Eaton Series C complete molded case circuit breaker	TERMINALS	Load side
CATALOG NUMBER	EHD3030	FRAME	F
UPC	786679317099	FREQUENCY RATING	50/60 Hz
PRODUCT LENGTH/DEPTH	3.38 in	INTERRUPT RATING	14 kAIC at 480 Vac 18 kAIC at 240 Vac
PRODUCT HEIGHT	6 in	NUMBER OF POLES	Three-pole
PRODUCT WIDTH	4.13 in		
PRODUCT WEIGHT	4.5 lb		
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.		
CERTIFICATIONS	UL Listed		