

Specifications



Photo is representative



Eaton EHD3030

Eaton Series C complete molded case circuit breaker, F-frame, EHD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 30 A, Load side, 50/60 Hz

Product specifications

AMPERAGE RATING	30 A
TRIP TYPE	T186
CIRCUIT BREAKER TYPE	EHD
CIRCUIT BREAKER FRAME TYPE	Complete breaker
SERIES	Series C

General specifications

PRODUCT NAME	Eaton Series C complete molded case circuit breaker	TERMINALS	Load side
CATALOG NUMBER	EHD3030	FRAME	F
UPC	786679317099	FREQUENCY RATING	50/60 Hz
PRODUCT LENGTH/DEPTH	3.38 in	INTERRUPT RATING	14 kAIC at 480 Vac 18 kAIC at 240 Vac
PRODUCT HEIGHT	6 in	NUMBER OF POLES	Three-pole
PRODUCT WIDTH	4.13 in		
PRODUCT WEIGHT	4.5 lb		
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.		
CERTIFICATIONS	UL Listed		