



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EL296 3/4" 90D Female/Male Elbow *Crouse-Hinds*

Catalog Number	EL296
Manufacturer	Crouse-Hinds
Description	90° Elbow, 3/4 In Trade Size, EI Model, Angle Shape, Electro Galvanized and Aluminum Acrylic Paint, Female to Male Connection, 0.56 LB/Ea
Weight per unit	0.5600 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Male Threaded, Female Threaded
dimensions	1.5000 IN X 2.5600 IN X 3.2000 IN

Descriptions

Description	3/4" 90D FEMALE/MALE ELBOW
extra long description	CRS-H EL296 3/4 NPT IRON 90 DEG MAL
Features	Crouse-Hinds series explosionproof unions are installed in rigid/IMC conduit systems to connect conduit to conduit, a conduit fitting, junction box or device enclosure. Expansion unions are also available, which allow for expansion and contraction of conduit and compensate for conduit cut too short. Available in a variety of materials, including stainless steel, to suit customer preferences. Explosionproof elbows allow for a 90° change in direction to the conduit run, or when terminating at a box or fit

Manufacturer Information

Brand	Eaton
GTIN	00782274308203
UPC	782274308203

Taxonomies, Classifications, and Categories

Category Description	RIGID ELBOWS
Type	ELBOW

Packaging

Carton	10
Weight Per each	0.56

Uses, Certifications, and Standards

Enclosure	Class I Div 1 2 Group A B C D, Class II Div 1 Group E F G, Class II Div 2 Group F G, Class III
standard	UL 886, CSA C22.2