



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ELL4G Ocal 4", 90D 40MIL PVC CTD HDG Rigid Elbow

Abb Installation Products, Inc

Catalog Number	ELL4G
Manufacturer	Abb Installation Products, Inc
Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 4 Inch/103 Metric, Angle 90 Degrees, Radius 16 Inch/406.40 Millimeters, Offset 21-3/4 Inch/552.45 Millimeters, Straight End 5-3/4 Inch/146.05 Millimeters, Unbent Length 36.63 Inch/930.47 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Weight per unit	33.1 (lbs/each)
Product Category	Steel

Material, Color, and Finish

Color	Gray
Finish	Hot Dip Galvanized

Dimensions and Weight

Depth	36.63
-------	-------

Descriptions

Description	OCAL 4", 90D 40MIL PVC CTD HDG RIGID ELBOW
extra long description	ABB ELL4-G PVC CTD ELBOW 90D 4IN ST
Long Description	Standard Radius Elbow, 40 Mil PVC Coated, Pipe Size 4 Inch/103 Metric, Angle 90 Degrees, Radius 16 Inch/406.40 Millimeters, Offset 21-3/4 Inch/552.45 Millimeters, Straight End 5-3/4 Inch/146.05 Millimeters, Unbent Length 36.63 Inch/930.47 Millimeters, Hot-Dip Galvanized Rigid Steel, Gray
Product Type	PVC CTD Elbow 90D 4IN Steel Gray
Special Features	Color-Coded Thread Protectors for Easy Identification of Conduit Size

Manufacturer Information

Brand	OCAL
GTIN	00704508370688
Manufacturers Part Number	ELL4-G
UPC	704508370688

Taxonomies, Classifications, and Categories

Category Description	Plastibond, Fiberglass Conduit & Fittings
Type	Conduit Elbow - Standard Radius

Trade Size

Trade Size	4 in , 103 mm
------------	---------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	33.12

Uses, Certifications, and Standards

Application	To Change Direction for Threaded, Rigid Conduit or When Terminating at a Box or Fitting
standard	cULus E46453, CSA