



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EM3731 3/4 HP 1075 RPM 208/230V Ball Bearing Shaft 1/2"X6

Precision Electric Motor

Catalog Number	EM3731
Manufacturer	Precision Electric Motor
Description	60 Hertz Frequency Rating; UI, Csa Approval; Condenser Fan Application; 208 to 230 Volt Ac 1-Phase Voltage Rating; Extended Stud Mounting; 18 Pound Weight; 3/4 HP Power Rating; 1075 RPM Speed Rating; Teao Enclosure Type; Rolled Steel Frame Material; B Insulation Class; 4.6 to 5.3 Amp Motor Fla; Yes Reversible; 1 Service Factor; 48 Nema Frame Size; Economaster[R] Brand; Type Induction Run, Permanent Split Capacitor; Shaft Type Double Flat; Bearing Type Ball (Drive End); Number Of Poles 6; Overall Dimension
Weight per unit	18.0 (lbs/each)
Product Category	20190723150330

Descriptions

Description	3/4 HP 1075 RPM 208/230V BALL BEARING SHAFT 1/2"X6
Long Description	60 HERTZ FREQUENCY RATING; UL, CSA APPROVAL; CONDENSER FAN APPLICATION; 208 TO 230 VOLT AC 1-PHASE VOLTAGE RATING; EXTENDED STUD MOUNTING; 18 POUND WEIGHT; 3/4 HP POWER RATING; 1075 RPM SPEED RATING; TEAO ENCLOSURE TYPE; ROLLED STEEL FRAME MATERIAL; B INSULATION CLASS; 4.6 TO 5.3 AMP MOTOR FLA; YES REVERSIBLE; 1 SERVICE FACTOR; 48 NEMA FRAME SIZE; ECONOMASTER[R] BRAND; TYPE INDUCTION RUN, PERMANENT SPLIT CAPACITOR; SHAFT TYPE DOUBLE FLAT; BEARING TYPE BALL (DRIVE END); NUMBER OF POLES 6; OVERALL DIMENSION
Product Type	Oem Motor

Manufacturer Information

Brand	
GTIN	00786674019585
Manufacturers Part Number	3S018
UPC	786674019585

Taxonomies, Classifications, and Categories

Category Description	Generic HAVCR Motors
----------------------	----------------------

Packaging

Carton	1
Weight Per each	18