

---

## 6X4 BASIC VALUE COMBO KIT

EN1022 | [On-Q](#)

---

### FEATURES & BENEFITS

Kit includes a 14" enclosure and a 6x4 Basic Combination Module (364400-04) allowing distribution of up to six telecom outlets with up to four lines each and incoming video signals to up to four television outlets. The Kit features 18" of unused rail space for additional On-Q modules for system expansion.



- Space-saving combination module distributes telephone and video signals
- UL Listed
- Can be either surface-mount or flush-mount
- Integrated ground screw
- Central hub for distribution and management of incoming services
- Features 18" of unused rail space for additional On-Q modules for system expansion
- Cover included

---

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Cat5e and RG6  
Color: White/Black  
Finish: Powder Coat  
Type: Telecom/Video Module w/Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: CSA-C22.2 No. 144.1 (2006), CAN/CSA-C22.2 No. 182.4-1990  
CSA Standard: Yes  
cULus: Yes  
UL Listing No: ANSI/UL 1863, ANSI/UL 985, ULC-S545, ANSI/UL 1023  
UL Standard: Yes

UN SPSC: 43222819

## CONSTRUCTION INFORMATION

Installation Location: In-Wall

## DIMENSIONS

Depth (Metric): 9.4 cm

Depth (US): 3.7"

Height (Metric): 35.8 cm

Height (US): 14.1"

Width (Metric): 36.3 cm

Width (US): 14.3 in

## TECHNICAL INFORMATION

Connection Method: 110 Punchdown and F

Humidity: 90% Relative Humidity (Non-Condensing)

Material: CRS

Mounting: Surface or Flush

Operating Temperature (Celsius): 0°C to 50°C

Output And Line Out Connection: 6 Telecom x 4 Video

---

## 6X4 BASIC VALUE COMBO KIT

EN1022 | [On-Q](#)

---

### FEATURES & BENEFITS

Kit includes a 14" enclosure and a 6x4 Basic Combination Module (364400-04) allowing distribution of up to six telecom outlets with up to four lines each and incoming video signals to up to four television outlets. The Kit features 18" of unused rail space for additional On-Q modules for system expansion.



- Space-saving combination module distributes telephone and video signals
- UL Listed
- Can be either surface-mount or flush-mount
- Integrated ground screw
- Central hub for distribution and management of incoming services
- Features 18" of unused rail space for additional On-Q modules for system expansion
- Cover included

---

### SPECIFICATIONS

#### GENERAL INFO

Cable Type: Cat5e and RG6  
Color: White/Black  
Finish: Powder Coat  
Type: Telecom/Video Module w/Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: CSA-C22.2 No. 144.1 (2006), CAN/CSA-C22.2 No. 182.4-1990  
CSA Standard: Yes  
cULus: Yes  
UL Listing No: ANSI/UL 1863, ANSI/UL 985, ULC-S545, ANSI/UL 1023  
UL Standard: Yes

UN SPSC: 43222819

## CONSTRUCTION INFORMATION

Installation Location: In-Wall

## DIMENSIONS

Depth (Metric): 9.4 cm

Depth (US): 3.7"

Height (Metric): 35.8 cm

Height (US): 14.1"

Width (Metric): 36.3 cm

Width (US): 14.3 in

## TECHNICAL INFORMATION

Connection Method: 110 Punchdown and F

Humidity: 90% Relative Humidity (Non-Condensing)

Material: CRS

Mounting: Surface or Flush

Operating Temperature (Celsius): 0°C to 50°C

Output And Line Out Connection: 6 Telecom x 4 Video