

---

## 30" PLASTIC HINGED DOOR, ONLY (PACK OF 5)

ENP3060-5 | [On-Q](#)



---

### FEATURES & BENEFITS

This standalone hinged door is designed to be purchased in the project trim-out phase to complete installation of the structured wiring assembly.

The door attaches easily to the ENP3080 plastic enclosure with provided screws and extra venting to allow for superior heat dissipation. [Click here](#) to learn more about the unique features that will save you time and simplify installation.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Adds 1.2" of depth for cable headroom and 3rd party device compatibility.
- Extra venting along the vertical plane allows for superior heat dissipation.
- Doors stack efficiently for efficient transportation and warehousing.
- Lockable with provided screws.
- Covers drywall hole for clean finish.
- UL listed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*

Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and

Rack Systems UL 985, Household Fire-Warning System Units ULC-S545, Residential Fire Warning System Control Units UL 1023, Household Burglar-Alarm System Units ULC/ORD-C1023, Household Burglar Alarm System Units  
UL Standard: Yes

## **CONSTRUCTION INFORMATION**

Material 1: ABS Plastic

## **DIMENSIONS**

Depth (Metric): 43 mm

Depth (US): 1.68"

Height (Metric): 807mm

Height (US): 31.75"

Width (Metric): 496 mm

Width (US): 15.97"

Product Weight (Metric): 6.25 kg

Product Weight (US): 13.75 lbs

## **TECHNICAL INFORMATION**

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C

---

## 30" PLASTIC HINGED DOOR, ONLY (PACK OF 5)

ENP3060-5 | [On-Q](#)



---

### FEATURES & BENEFITS

This standalone hinged door is designed to be purchased in the project trim-out phase to complete installation of the structured wiring assembly.

The door attaches easily to the ENP3080 plastic enclosure with provided screws and extra venting to allow for superior heat dissipation. [Click here](#) to learn more about the unique features that will save you time and simplify installation.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Adds 1.2" of depth for cable headroom and 3rd party device compatibility.
- Extra venting along the vertical plane allows for superior heat dissipation.
- Doors stack efficiently for efficient transportation and warehousing.
- Lockable with provided screws.
- Covers drywall hole for clean finish.
- UL listed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*

Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and

Rack Systems UL 985, Household Fire-Warning System Units ULC-S545, Residential Fire Warning System Control Units UL 1023, Household Burglar-Alarm System Units ULC/ORD-C1023, Household Burglar Alarm System Units  
UL Standard: Yes

## **CONSTRUCTION INFORMATION**

Material 1: ABS Plastic

## **DIMENSIONS**

Depth (Metric): 43 mm

Depth (US): 1.68"

Height (Metric): 807mm

Height (US): 31.75"

Width (Metric): 496 mm

Width (US): 15.97"

Product Weight (Metric): 6.25 kg

Product Weight (US): 13.75 lbs

## **TECHNICAL INFORMATION**

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C