



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6510 Broadway St
77554-0000, TX Galveston
Phone: 409-741-0072
Fax: 409-741-0433



EREGYTWPSQM12 Twin Lamp Heads Weather Proof Square Grey

Lithonia Lighting - Acuity

Catalog Number	EREGYTWPSQM12
Manufacturer	Lithonia Lighting - Acuity
Description	The Lithonia Lighting® Gray Ere Led Remotes Are Suitable For Outdoor Lighting Applications, For Use As Part Of An Emergency Lighting System, Illuminating The Path Of Egress. These Twin Led Lamp Remotes Are Fully Adjustable and Are Suitable For Wall or Ceiling Mounting.
Weight per unit	2.0 (lbs/each)
Product Category	Emergency Lighting

Features

average life	100,000
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	85 LM
Material	Thermoplastic
Maximum Operating Temperature	50
Power Source	Hardwired
Shape	Square
Warranty	2

Material, Color, and Finish

Color	Gray
color temperature	6500
Finish	Textured
Lens Color	Clear
Lens Material	Plastic

Dimensions and Weight

Height	4.5
Length	10.5
Width	7.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6510 Broadway St
77554-0000, TX Galveston
Phone: 409-741-0072
Fax: 409-741-0433

Descriptions

Construction	New Construction,Remodel
Description	TWIN LAMP HEADS WEATHER PROOF SQUARE GREY
extra long description	LITH ERE GY T WP SQ M12 Remote, Gre
Long Description	The Lithonia Lighting® gray ERE LED Remotes are suitable for outdoor lighting applications, for use as part of an emergency lighting system, illuminating the path of egress. These twin LED lamp remotes are fully adjustable and are suitable for wall or ceiling mounting.
Product Type	Remote Light Head

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00191848036815
Manufacturers Part Number	ERE GY T WP SQ M12
UPC	191848036815

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
----------------------	--------------------------

Packaging

Carton	1
Package	12
Weight	2
Weight Per each	2

Uses, Certifications, and Standards

Application	Education,Hospitality,Offices & Banks,Retail
environmental conditions	Indoor,Outdoor
Mounting	SURFACE
standard	C-UL-US,NFPA 101,NFPA 70,UL