



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EREWSGLRDM24 SNGL Remote RND Emgy Head WHT

Lithonia Lighting

Catalog Number	EREWSGLRDM24
Manufacturer	Lithonia Lighting
Description	The Lithonia Lighting® Ere Led Remotes Are Suitable For Indoor Lighting Applications, For Use As Part Of An Emergency Lighting System, Illuminating The Path Of Egress. These Single Led Lamp Remotes Are Fully Adjustable and Are Suitable For Wall or Ceiling Mounting.
Weight per unit	1.0 (lbs/each)
Product Category	Emergency Lighting

Features

average life	100,000
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
lumens	76 LM
Material	Thermoplastic
Maximum Operating Temperature	40
Power Source	Hardwired
Shape	Round
Warranty	2

Material, Color, and Finish

Color	White
Finish	Matte
Lens Color	Clear
Lens Material	Plastic

Dimensions and Weight

Height	2.5
Length	6
Width	5.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	New Construction,Remodel
Description	SNGL REMOTE RND EMGCY HEAD WHT
extra long description	LITH ERE W SGL RD M24 Remote, White
Long Description	The Lithonia Lighting® ERE LED Remotes are suitable for indoor lighting applications, for use as part of an emergency lighting system, illuminating the path of egress. These single LED lamp remotes are fully adjustable and are suitable for wall or ceiling mounting.
Product Type	Remote Light Head

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00191848041314
Manufacturers Part Number	ERE SGL M24
UPC	191848041314

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
----------------------	---------------------------

Packaging

Carton	1
Package	24
Weight	0.5
Weight Per each	1

Uses, Certifications, and Standards

Application	Education,Hospitality,Offices & Banks,Retail
environmental conditions	Indoor
Mounting	SURFACE
standard	C-UL-US,NFPA 101,NFPA 70,UL