



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EV1010RBQ 12-10AWG 1/5"STD Ylw Insltd Ring TRML *Panduit Corporation*

Catalog Number	EV1010RBQ
Manufacturer	Panduit Corporation
Description	Stronghold EV10-10RB-Q Contractor Grade Vinyl Insulated Ring Terminals Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. Accommodates 12-10 Awg Wire Gauge, Compatible With #10 Stud, Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

insulation	Vinyl
Material	Copper
media	Yes
Voltage Rating	600
Wire Size	#10

### Material, Color, and Finish

Color	Yellow
Finish	Tinned

### Dimensions and Weight

Size	#10
------	-----

### Descriptions

Description	12-10AWG 1/5"STD YLW INSLTD RING TRML
extra long description	PAN EV10-10RB-Q StrongHold™ EV10-10
Long Description	StrongHold EV10-10RB-Q Contractor Grade Vinyl Insulated Ring Terminals are a reliable and economical option that withstand a wide range of general-purpose applications. Accommodates 12-10 AWG wire gauge, compatible with #10 Stud, are yellow in color, and come in packages of 25.
Product Type	Stronghold™ EV10-10RB-Q Ring Terminal, Yellow, Vinyl, 1/5" S

### Manufacturer Information

Brand	Panduit®
GTIN	00074983281855
Manufacturers Part Number	EV10-10RB-Q
UPC	074983281855



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... TERMINALS

Type ..... Ring Terminal

## Availability

minimum qty ..... 25

## Packaging

Carton ..... 25

Package ..... 250

Weight Per each ..... 0.05

## Uses, Certifications, and Standards

Mounting ..... 0.31

standard ..... CSA Certified LR31212;UL Listed 587H E52164