



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F032865ECO 32W 48" T8 65K 80CRI 2850LM *Sylvania-Ledvance*

Catalog Number	F032865ECO
Manufacturer	Sylvania-Ledvance
Description	32W, 48 Inch Mol, T8 Octron Fluorescent Lamp, 6500K Color Temperature, Rare Earth Phosphor, 80 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.4200 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	30000
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
lumens	2850
Shape	T8
Wattage	32

Material, Color, and Finish

color rendering index (cri)	81
color temperature	6500

Descriptions

Description	32W 48" T8 65K 80CRI 2850LM
extra long description	SYL FO32865ECO/24811 FO32865ECO 30/
Long Description	32W, 48 inch MOL, T8 OCTRON fluorescent lamp, 6500K color temperature, rare earth phosphor, 80 CRI, suitable for IS or RS operation, ECOLOGIC
Product Type	FO32865ECO 30/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135248115
Manufacturers Part Number	FO32/865/ECO/24811
UPC	046135248115

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Flourescent

Packaging

Carton	1
Package	30
Weight Per each	0.42