



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F096841ECO 96W T8 96" 4100K 82cri

Sylvania-Ledvance

Catalog Number	F096841ECO
Manufacturer	Sylvania-Ledvance
Description	59W, 96" Mol, T8 Octron Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 82 Cri, Suitable For Is Operation, Ecologic
Weight per unit	0.9200 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Single Pin
bulb type	T8
Lamp Type	INSTANT START
lumens	5900
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent

Material, Color, and Finish

color rendering index (cri)	82
color temperature	4100
Finish	Phosphor Coated

Descriptions

Description	96W T8 96" 4100K 82CRI
extra long description	SYL FO96841ECO/22149 FO96841ECO 24/
Long Description	59W, 96" MOL, T8 OCTRON fluorescent lamp, 4100K color temperature, rare earth phosphor, 82 CRI, suitable for IS operation, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221491
Manufacturers Part Number	FO96/841/ECO/22149
UPC	046135221491

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	24
Weight Per each	0.92