



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F096850ECO 59W T8 96" 5000K 80 Cri Single Pin Energy Saving

Sylvania-Ledvance

Catalog Number	F096850ECO
Manufacturer	Sylvania-Ledvance
Description	59W, 96" Mol, T8 Octron Fluorescent Lamp, 5000K Color Temperature, Rare Earth Phosphor, 80 Cri, Suitable For Is Operation, Ecologic
Weight per unit	0.9200 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	15000
Base	Single Pin
Lamp Type	INSTANT START
lumens	5900
Shape	T8
start type	Instant Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	59

Material, Color, and Finish

color rendering index (cri)	80
color temperature	5000
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1
Length	94

Descriptions

Description	59W T8 96" 5000K 80 CRI SINGLE PIN ENERGY SAVING
extra long description	SYL FO96/850/ECO/22173 FO96850ECO 2
Long Description	59W, 96" MOL, T8 OCTRON fluorescent lamp, 5000K color temperature, rare earth phosphor, 80 CRI, suitable for IS operation, ECOLOGIC
Product Type	FO96850ECO 24/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221736
Manufacturers Part Number	FO96/850/ECO/22173
UPC	046135221736



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Fluorescent

Type FLUORESCENT

Packaging

Carton 1

Package 24

Weight Per each 0.92

Uses, Certifications, and Standards

Application Commercial/Residential