



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F2037 #14, .984L Blu Insld Pin TRML

*Abb Installation Products, Inc*

|                  |   |
|------------------|---|
| Catalog Number   | F2037   |
| Manufacturer     | Abb Installation Products, Inc                              |
| Description      | Insulated Ferrule, Copper Material, 0.984 In Overall Length |
| Weight per unit  | 0.0010 (lbs/each)   |
| Product Category | Power BLKS & Distribution BLKS                              |

### Features

|           |        |
|-----------|--------|
| Wire Size | 14 AWG |
|-----------|--------|

### Material, Color, and Finish

|       |      |
|-------|------|
| Color | Blue |
|-------|------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | #14,.984L BLU INSLTD PIN TRML  |
| extra long description | ABB F2037 INS PP FERRULE 14, 2.5 MM  |
| Special Features       | Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks |

### Manufacturer Information

|      |                |
|------|----------------|
| GTIN | 00786210335179 |
| UPC  | 786210335179   |

### Taxonomies, Classifications, and Categories

|                      |                                 |
|----------------------|---------------------------------|
| Category Description | TERMINALS                       |
| Type                 | Polypropylene Insulated Ferrule |

### Availability

|             |     |
|-------------|-----|
| minimum qty | 500 |
|-------------|-----|

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 500   |
| Weight Per each | 0.001 |

### Uses, Certifications, and Standards

|          |                         |
|----------|-------------------------|
| standard | UL E489056 / UL E489056 |
|----------|-------------------------|