



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F20T12DECO 20W T12 24" Daylight 76 Cri Bi-Pin Fluor Lamp

Ge By Current Lamps

Catalog Number	F20T12DECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 20 WTT, 1025 LM, 6500 KV, 75 Cri, 1.5 In Diameter, 24 In Length, Medium Bi-Pin (G13) Base, 9000 HR Average Life
Weight per unit	0.3700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	9000.0
Base	Medium Bi-Pin (G13)
lumens	1025.0
Wattage	20.0

Material, Color, and Finish

color rendering index (cri)	75.0
color temperature	6500.0

Dimensions and Weight

Diameter	1.5
Length	24.0

Descriptions

Description	20W T12 24" DAYLIGHT 76 CRI BI-PIN FLUOR LAMP
extra long description	GEL F20T12/D/ECO 80047 SLIM LINE /
Long Description	GE Ecolux®, 20 WTT, 1025 LM, 6500 KV, 75 CRI, 1.5 IN Diameter, 24 IN Length, Medium Bi-Pin (G13) Base, 9000 HR Average Life
Product Type	80047 Slim Line / F20

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168800471
Manufacturers Part Number	F20T12/D/ECO
UPC	043168800471

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	24
Weight Per each	0.37

Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------