



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F24T12CWHO 35W T12 24" High Output Cool White 62 Cri R17D Pin

*Sylvania-Ledvance*

Catalog Number	F24T12CWHO
Manufacturer	Sylvania-Ledvance
Description	35W, 24" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri
Weight per unit	0.3500 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	9000
Base	Recessed Double Contact
Lamp Type	RAPID START
lumens	1,650
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage	41.00 V
Voltage Rating	Ballast Dependent
Wattage	35

### Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1.5 in
----------	--------

### Descriptions

Description	35W T12 24" HIGH OUTPUT COOL WHITE 62 CRI R17D PIN
extra long description	SYL F24T12/CW/HO/25313 F24T12CWHO 3
Long Description	35W, 24" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI
Product Type	F24T12CWHO 30/CS 1/Sku
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135253133
Manufacturers Part Number	F24T12/CW/HO/25313
UPC	046135253133



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 30

Weight Per each ..... 0.35

## Uses, Certifications, and Standards

Application ..... Commercial/Residential