



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F25T8SP30ECO 25W T8 36" 3000K 78 Cri Bi-Pin Energy Saving

*Ge By Current Lamps*

Catalog Number	F25T8SP30ECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 25 WTT, 2080 LM, 3000 KV, 78 Cri, 1 In Diameter, 35.78 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Weight per unit	0.3500 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

average life	30000.0
Base	Medium Bi-Pin (G13)
lumens	2080.0
Wattage	25.0

### Material, Color, and Finish

color rendering index (cri)	78.0
color temperature	3000.0

### Dimensions and Weight

Diameter	1.0
Length	35.78

### Descriptions

Description	25W T8 36" 3000K 78 CRI BI-PIN ENERGY SAVING
extra long description	GEL F25T8/SP30/ECO 45750 FLUORESCEN
Long Description	GE Ecolux®, 25 WTT, 2080 LM, 3000 KV, 78 CRI, 1 IN Diameter, 35.78 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Product Type	45750 Fluorescent

### Manufacturer Information

Brand	GE Current, a Daintree company
GTIN	00043168457507
Manufacturers Part Number	F25T8/SP30/ECO
UPC	043168457507

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Weight Per each	0.35

### Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------