

Home > Air > Fitters > Universal Fitters > F300-W

F300-W



Casual

Modern

Outdoor

Traditional

Youth

Contractor

Bathroom Ventilation

Type 1 Blades

Type 2 Blades

Type 3 Blades

Type 4 Blades

Type 5 Blades

Bowl Kits

Complete Light Kits

Fitters

Glass

Specs

Bulb Type: Medium Base CFL

Bulb Type: Candelabra Bulbs

Max. Watt: 3-60W

Max. Watt: 3-13W CFL (Included)

EPACT Model: F300CFL-(Finish)

Height: 3.0"

Width: 6.5"

Available Finishes

Finish:



Better By Design

Ceiling Fan Finishes



AB
Antique Brass



AL
Almond



AW
Antique White



BN
Brushed Nickel



BR
Brown



BS
Brownstone



BZ
Bronze Verdi



CF
Carbon Fiber




CH
Chrome



EB
European Bronze



ET
English Toffee




FB
Flat Black



GS
Graystone



GV
Galvanized Steel



HG
Hunter Green



MO
Mocha



OB
Oiled Bronze



OI
Old Iron



PB
Polished Brass



PE
Pearl Essence



PT
Pewter



RB
Royal Blue



RD
Red



RI
Rustic Iron



RT
Rust



SW
Sandstone White



TW
Textured White



VG
Verdi Green



W
White

EditRegion5