



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

F30T12CWHO *Delisted* 42W T12 30" Ho CW 62 Cri R17D Pin

Sylvania-Ledvance

Catalog Number	F30T12CWHO
Manufacturer	Sylvania-Ledvance
Description	OBS25322 42W, 30" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri
Weight per unit	0.4300 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
lumens	2,250
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	42

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in
----------	--------

Descriptions

Description	*DELISTED* 42W T12 30" HO CW 62 CRI R17D PIN
extra long description	SYL F30T12/CW/HO/25322 F30T12CWHO 3
Long Description	OBS25322 42W, 30" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135253225
Manufacturers Part Number	F30T12/CW/HO/25322
UPC	046135253225

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4250 Business Center Dr. Suite 300
28214-0000, NC Charlotte
Phone: 980-249-1969
Fax: 704-900-0948

Packaging

Carton	1
Package	30
Weight Per each	0.43