



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F31T8SPX41UEC0 31W T8 U Bend 4100K Med Bi-Pin 82 Cri Fluor Lamp

Ge By Current Lamps

Catalog Number	F31T8SPX41UEC0
Manufacturer	Ge By Current Lamps
Description	Ge, 31 WTT, 2775 LM, 4100 KV, 82 Cri, 1 In Diameter, 22.5 In Length, Medium Bi-Pin (G13) Base, 24000 HR Average Life
Weight per unit	0.6200 (lbs/each)
Product Category	Shape Lamps

Features

average life	24000
Base	Medium Bi-Pin (G13)
lumens	2775
Wattage	31

Material, Color, and Finish

color rendering index (cri)	82.0
color temperature	4100.0

Dimensions and Weight

Diameter	1
Length	22.5

Descriptions

Description	31W T8 U BEND 4100K MED BI-PIN 82 CRI FLUOR LAMP
extra long description	GEL F31T8SPX41/U/ECO 72119 FLUORESC
Long Description	GE, 31 WTT, 2775 LM, 4100 KV, 82 CRI, 1 IN Diameter, 22.5 IN Length, Medium Bi-Pin (G13) Base, 24000 HR Average Life
Product Type	72119 Fluorescent

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168721196
Manufacturers Part Number	F31T8SPX41/U/ECO
UPC	043168721196

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	15
Weight Per each	0.62

Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------