



GE
Lighting

66474 - F34/CX41/WM/ECO

F34/CX41/WM/ECO-T8-SPP NEW TECHNICAL LAMPS



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T12
Base	Medium Bi-Pin (G13)
Rated Life	20000.0 hrs
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
LEED-EB MR Credit	114 picograms Hg per mean lumen hour
Primary Application	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	2500.0
Mean Lumens	2200.0
Nominal Initial Lumens per Watt	73
Color Temperature	4100.0 K
Color Rendering Index (CRI)	87.0

ELECTRICAL CHARACTERISTICS

Wattage	34.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

PRODUCT INFORMATION

Product Code	66474
Description	F34/CX41/WM/ECO
Standard Package	Case
Standard Package GTIN	10043168664742
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168664745



GE
Lighting

66474 - F34/CX41/WM/ECO

F34/CX41/WM/ECO-T8-SPP NEW TECHNICAL LAMPS



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T12
Base	Medium Bi-Pin (G13)
Rated Life	20000.0 hrs
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
LEED-EB MR Credit	114 picograms Hg per mean lumen hour
Primary Application	Energy Saving

PHOTOMETRIC CHARACTERISTICS

Initial Lumens	2500.0
Mean Lumens	2200.0
Nominal Initial Lumens per Watt	73
Color Temperature	4100.0 K
Color Rendering Index (CRI)	87.0

ELECTRICAL CHARACTERISTICS

Wattage	34.0
---------	------

DIMENSIONS

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

PRODUCT INFORMATION

Product Code	66474
Description	F34/CX41/WM/ECO
Standard Package	Case
Standard Package GTIN	10043168664742
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168664745