



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F36T12CWHO 45W T12 36" Cool White High Output 62 Cri R17D Pin

Sylvania-Ledvance

Catalog Number	F36T12CWHO
Manufacturer	Sylvania-Ledvance
Description	OBS25333 45W, 36" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri
Weight per unit	0.5200 (lbs/each)
Product Category	Lighting

Features

amperage rating	Ballast Dependent
average life	9000
Base	Recessed Double Contact
lumens	2850 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	45

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in
----------	--------

Descriptions

Description	45W T12 36" COOL WHITE HIGH OUTPUT 62 CRI R17D PIN
extra long description	SYL F36T12/CW/HO/25333 F36T12CWHO 3
Long Description	OBS25333 45W, 36" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI
Product Type	F36T12CWHO 30/CS 1/Sku
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135253331
Manufacturers Part Number	F36T12/CW/HO/25333
UPC	046135253331



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.52

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------