



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2703 Hancock Dr.  
76504-0000, TX Temple  
Phone: 254-899-2800  
Fax: 254-899-2805



## **F40T8SPX41 \*Delisted\* 40W T8 60" 41K Med Bi-Pin 84 Cri Fluor**

*Ge By Current Lamps*

Catalog Number	F40T8SPX41
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, Medium Bi-Pin (G13) Base, T8 Bulb Shape, 84, 20000 H Average Life, 4100 K, 40 W, 3725 LM Brightness (Lumens), Soda Lime Housing Material, 1.0 In Diameter, 60 In Length, Rapid, +10 °C Operating Temperature, 0.654 LB/Ea
Weight per unit	0.6540 (lbs/each)
Product Category	Linear Fluorescent Straight La

### **Features**

Base	Medium Bi-Pin (G13)
lumens	3725.0
Wattage	40.0

### **Material, Color, and Finish**

color rendering index (cri)	84.0
-----------------------------	------

### **Descriptions**

Description	*DELISTED* 40W T8 60" 41K MED BI-PIN 84 CRI FLUOR
-------------	---

### **Manufacturer Information**

Brand	GE Current
GTIN	00043168226622
Manufacturers Part Number	F40T8/SPX41
UPC	043168226622

### **Taxonomies, Classifications, and Categories**

Category Description	Fluorescent
----------------------	-------------

### **Availability**

Manufacturer Status	Inactive
Status	Inactive

### **Packaging**

Carton	1
Package	24
Weight Per each	0.654