



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F48T12DH0 60W T12 48" Daylight High Output 76 Cri R17D

*Sylvania-Ledvance*

Catalog Number	F48T12DH0
Manufacturer	Sylvania-Ledvance
Description	60W, 48" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 72 Cri
Weight per unit	0.6800 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	12000
Base	Recessed Double Contact
bulb type	T12
Lamp Type	RAPID START
lumens	3600 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	60

### Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1.5 in
----------	--------

### Descriptions

Description	60W T12 48" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	SYL F48T12DH0/25150 F48T12DH0 30/CS
Long Description	60W, 48" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 72 CRI
Product Type	F48T12DH0 30/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251504
Manufacturers Part Number	F48T12/D/HO/25150
UPC	046135251504



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

## Packaging

Carton	1
Package	30
Weight Per each	0.68

## Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------