



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F54T5841HOECOCVG 54W T5H0 45" 41K 4850LM

Ge By Current Lamps

Catalog Number	F54T5841HOECOCVG
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 54 WTT, 4850 LM, 4100 KV, 85 Cri, 0.625 In Diameter, 45.2 In Length, Miniature Bi-Pin (G5) Base, 30000 HR Average Life
Weight per unit	0.3900 (lbs/each)
Product Category	Shatter Resistant Fluorescent

Features

average life	30000.0
Base	Miniature Bi-Pin (G5)
lumens	4850.0
Wattage	54.0

Material, Color, and Finish

color rendering index (cri)	85.0
color temperature	4100.0

Dimensions and Weight

Diameter	0.625
Length	45.2

Descriptions

Description	54W T5H0 45" 41K 4850LM
extra long description	GEL F54T5841HOECOCVG 48458 FLUORESC
Long Description	GE Ecolux®, 54 WTT, 4850 LM, 4100 KV, 85 CRI, 0.625 IN Diameter, 45.2 IN Length, Miniature Bi-Pin (G5) Base, 30000 HR Average Life
Product Type	48458 Fluorescent

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168484589
Manufacturers Part Number	F54T5841HOECOCVG
UPC	043168484589

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	40
Weight Per each	0.39



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Shatter-Resistant