



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F60T12DHO *Delisted* 75W T12 60" Daylight Ho 76 Cri R17D

Sylvania-Ledvance

Catalog Number	F60T12DHO
Manufacturer	Sylvania-Ledvance
Description	OBS25120 75W, 60"Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 72 Cri
Weight per unit	0.8600 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	12000
Base	Recessed Double Contact
lumens	4600 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	75

Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in
----------	--------

Descriptions

Description	*DELISTED* 75W T12 60" DAYLIGHT HO 76 CRI R17D
extra long description	SYL F60T12/D/HO/25120 F60T12DHO 30/
Long Description	OBS25120 75W, 60"MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 72 CRI
Product Type	F60T12DHO 30/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251207
Manufacturers Part Number	F60T12/D/HO/25120
UPC	046135251207

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	30
Weight Per each	0.86

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------