



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F72T12DH0 85W T12 72" Daylight High Output 76 Cri R17D

*Sylvania-Ledvance*

Catalog Number	F72T12DH0
Manufacturer	Sylvania-Ledvance
Description	85W, 72" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 72 Cri
Weight per unit	1.1 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
bulb type	T12
lumens	5550 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	85

### Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500

### Descriptions

Description	85W T12 72" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	SYL F72T12/D/HO/25189 F72T12DHO 15/
Long Description	85W, 72" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 72 CRI

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251894
Manufacturers Part Number	F72T12/D/HO/25189
UPC	046135251894

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

### Packaging

Carton	1
Package	15
Weight Per each	1.08

### Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------